

Varistar CP EMC Shortened Door with Recessed Mounting Plate



Recessed connection plates are needed for connectors which don't protrude out of the plane of the cabinet

功能

Intelligent cable management design with recessed connection plates

Door with lever handle with push button

Door opening angle 180°

Connection plate is 400 mm high

For recessed plate: Plate recessed by 40 mm

技术参数

产品类型: 机柜门

防护等级: IP55

锁定类型: 多点锁定

材料: 钢; Stainless 钢

Table 1/1

物料号	机架高度	高度	宽度	包装数量	完成	快速发货
21630-903	38U	1800mm	600mm	1	粉末涂层	No
21630-904	38U	1800mm	800mm	1	粉末涂层	No

物料号	机架高度	高度	宽度	包装数量	完成	快速发货
21630-905	42U	2000mm	600mm	1	粉末涂层	No
21630-906	42U	2000mm	800mm	1	粉末涂层	No
21630-907	47U	2200mm	600mm	1	粉末涂层	No
21630-908	47U	2200mm	800mm	1	粉末涂层	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE