

Varistar CP 框架



符合静态承载要求的 Varistar 钢制框架。适用于 19" ETSI 或安装板集成。

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

功能

焊接, 表面粉末涂层, 黑灰色, RAL 7021

碳钢, 1.5 mm, 镀锌, 带中央接地点

静态承载能力最大 1600 千克

请单独订购可调节支脚

技术参数

静态负载: 1600kg

产品类型: 机柜/机架框架

材料: 钢

Table 1/2

物料号	机架高度	高度	宽度	深度	包装数量	颜色
20630-122	47U	2200mm	800mm	1200mm	1	暗灰色
20630-121	47U	2200mm	800mm	1100mm	1	暗灰色
20630-115	47U	2200mm	600mm	1100mm	1	暗灰色
20630-116	47U	2200mm	600mm	1200mm	1	暗灰色

物料号	机架高度	高度	宽度	深度	包装数量	颜色
20630-065	24U	1200mm	600mm	600mm	1	暗灰色
20630-066	24U	1200mm	600mm	800mm	1	暗灰色
20630-071	24U	1200mm	800mm	600mm	1	暗灰色
20630-072	24U	1200mm	800mm	800mm	1	暗灰色
20630-075	29U	1400mm	600mm	600mm	1	暗灰色
20630-076	29U	1400mm	600mm	800mm	1	暗灰色
20630-079	29U	1400mm	800mm	600mm	1	暗灰色
20630-080	29U	1400mm	800mm	800mm	1	暗灰色
20630-083	33U	1600mm	600mm	600mm	1	暗灰色
20630-084	33U	1600mm	600mm	800mm	1	暗灰色
20630-087	33U	1600mm	800mm	600mm	1	暗灰色
20630-088	33U	1600mm	800mm	800mm	1	暗灰色
20630-091	38U	1800mm	600mm	600mm	1	暗灰色
20630-092	38U	1800mm	600mm	800mm	1	暗灰色
20630-095	38U	1800mm	800mm	600mm	1	暗灰色
20630-096	38U	1800mm	800mm	800mm	1	暗灰色
20630-261	42U	2000mm	600mm	300mm	1	暗灰色

物料号	机架高度	高度	宽度	深度	包装数量	颜色
20630-099	42U	2000mm	600mm	600mm	1	暗灰色
20630-100	42U	2000mm	600mm	800mm	1	暗灰色
20630-101	42U	2000mm	600mm	900mm	1	暗灰色
20630-102	42U	2000mm	600mm	1000mm	1	暗灰色
20630-105	42U	2000mm	800mm	600mm	1	暗灰色
20630-106	42U	2000mm	800mm	800mm	1	暗灰色
20630-107	42U	2000mm	800mm	900mm	1	暗灰色
20630-108	42U	2000mm	800mm	1000mm	1	暗灰色
20630-262	47U	2200mm	600mm	300mm	1	暗灰色
20630-111	47U	2200mm	600mm	600mm	1	暗灰色
20630-112	47U	2200mm	600mm	800mm	1	暗灰色
20630-113	47U	2200mm	600mm	900mm	1	暗灰色
20630-114	47U	2200mm	600mm	1000mm	1	暗灰色
20630-117	47U	2200mm	800mm	600mm	1	暗灰色
20630-118	47U	2200mm	800mm	800mm	1	暗灰色
20630-119	47U	2200mm	800mm	900mm	1	暗灰色
20630-120	47U	2200mm	800mm	1000mm	1	暗灰色

物料号	机架高度	高度	宽度	深度	包装数量	颜色
20630-067	24U	1200mm	600mm	900mm	1	暗灰色
20630-068	24U	1200mm	600mm	1000mm	1	暗灰色
20630-073	24U	1200mm	800mm	900mm	1	暗灰色
20630-074	24U	1200mm	800mm	1000mm	1	暗灰色
20630-077	29U	1400mm	600mm	900mm	1	暗灰色
20630-078	29U	1400mm	600mm	1000mm	1	暗灰色
20630-081	29U	1400mm	800mm	900mm	1	暗灰色
20630-082	29U	1400mm	800mm	1000mm	1	暗灰色
20630-085	33U	1600mm	600mm	900mm	1	暗灰色
20630-086	33U	1600mm	600mm	1000mm	1	暗灰色
20630-089	33U	1600mm	800mm	900mm	1	暗灰色
20630-090	33U	1600mm	800mm	1000mm	1	暗灰色
20630-093	38U	1800mm	600mm	900mm	1	暗灰色
20630-094	38U	1800mm	600mm	1000mm	1	暗灰色
20630-097	38U	1800mm	800mm	900mm	1	暗灰色
20630-098	38U	1800mm	800mm	1000mm	1	暗灰色
20630-123	52U	2450mm	600mm	1000mm	1	暗灰色

物料号	机架高度	高度	宽度	深度	包装数量	颜色
20630-126	52U	2450mm	800mm	1000mm	1	暗灰色
20630-125	52U	2450mm	600mm	1200mm	1	暗灰色
20630-128	52U	2450mm	800mm	1200mm	1	暗灰色
20630-124	52U	2450mm	600mm	1100mm	1	暗灰色
20630-127	52U	2450mm	800mm	1100mm	1	暗灰色
20630-103	42U	2000mm	600mm	1100mm	1	暗灰色
20630-104	42U	2000mm	600mm	1200mm	1	暗灰色
20630-109	42U	2000mm	800mm	1100mm	1	暗灰色
20630-110	42U	2000mm	800mm	1200mm	1	暗灰色

Table 2/2						
物料号	颜色代码	符合	框架材料	类型	搭配	快速发货
20630-122	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-121	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-115	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-116	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-065	RAL 7021		钢	标准	Varistar CP	No
20630-066	RAL 7021		钢	标准	Varistar CP	No

物料号	颜色代码	符合	框架材料	类型	搭配	快速发货
20630-071	RAL 7021		钢	标准	Varistar CP	No
20630-072	RAL 7021		钢	标准	Varistar CP	No
20630-075	RAL 7021		钢	标准	Varistar CP	No
20630-076	RAL 7021		钢	标准	Varistar CP	No
20630-079	RAL 7021		钢	标准	Varistar CP	No
20630-080	RAL 7021		钢	标准	Varistar CP	No
20630-083	RAL 7021		钢	标准	Varistar CP	No
20630-084	RAL 7021		钢	标准	Varistar CP	No
20630-087	RAL 7021		钢	标准	Varistar CP	No
20630-088	RAL 7021		钢	标准	Varistar CP	No
20630-091	RAL 7021		钢	标准	Varistar CP	No
20630-092	RAL 7021		钢	标准	Varistar CP	No
20630-095	RAL 7021		钢	标准	Varistar CP	No
20630-096	RAL 7021		钢	标准	Varistar CP	No
20630-261	RAL 7021		钢	标准	Varistar CP	No
20630-099	RAL 7021		钢	标准	Varistar CP	No
20630-100	RAL 7021		钢	标准	Varistar CP	No

物料号	颜色代码	符合	框架材料	类型	搭配	快速发货
20630-101	RAL 7021		钢	标准	Varistar CP	No
20630-102	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-105	RAL 7021		钢	标准	Varistar CP	No
20630-106	RAL 7021		钢	标准	Varistar CP	No
20630-107	RAL 7021		钢	标准	Varistar CP	No
20630-108	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-262	RAL 7021		钢	标准	Varistar CP	No
20630-111	RAL 7021		钢	标准	Varistar CP	No
20630-112	RAL 7021		钢	标准	Varistar CP	No
20630-113	RAL 7021		钢	标准	Varistar CP	No
20630-114	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-117	RAL 7021		钢	标准	Varistar CP	No
20630-118	RAL 7021		钢	标准	Varistar CP	No
20630-119	RAL 7021		钢	标准	Varistar CP	No
20630-120	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-067	RAL 7021		钢	标准	Varistar CP	No
20630-068	RAL 7021		钢	标准	Varistar CP	No

物料号	颜色代码	符合	框架材料	类型	搭配	快速发货
20630-073	RAL 7021		钢	标准	Varistar CP	No
20630-074	RAL 7021		钢	标准	Varistar CP	No
20630-077	RAL 7021		钢	标准	Varistar CP	No
20630-078	RAL 7021		钢	标准	Varistar CP	No
20630-081	RAL 7021		钢	标准	Varistar CP	No
20630-082	RAL 7021		钢	标准	Varistar CP	No
20630-085	RAL 7021		钢	标准	Varistar CP	No
20630-086	RAL 7021		钢	标准	Varistar CP	No
20630-089	RAL 7021		钢	标准	Varistar CP	No
20630-090	RAL 7021		钢	标准	Varistar CP	No
20630-093	RAL 7021		钢	标准	Varistar CP	No
20630-094	RAL 7021		钢	标准	Varistar CP	No
20630-097	RAL 7021		钢	标准	Varistar CP	No
20630-098	RAL 7021		钢	标准	Varistar CP	No
20630-123	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-126	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-125	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No

物料号	颜色代码	符合	框架材料	类型	搭配	快速发货
20630-128	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-124	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-127	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-103	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-104	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-109	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No
20630-110	RAL 7021	IEC 61587-1, IEC 61587-3	钢	标准	Varistar CP	No

其他产品详情

可以将脚轮添加到框架中。如果您的应用需要脚轮，可以订购包含脚轮的移动框架。

25 24

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE