

# Varistar CP 钢板门, Plain With Multi-Point Locking, 尺寸缩短型



IP55 钢门配有杠杆手柄和最多 4 点锁定 (>2000 毫米)。

## 功能

连接板高度 400 毫米 带按钮的杠杆手柄

带按钮的摇柄锁

带按钮的摇柄锁

开启角度 180°

钢门最多可锁定 4 点

## 技术参数

产品类型: 机柜门

Table 1/2

| 物料号       | 机架高度 | 高度     | 宽度    | 防护等级 | 包装数量 | 颜色 |
|-----------|------|--------|-------|------|------|----|
| 21630-372 | 38U  | 1800mm | 600mm | IP55 | 1    |    |
| 21630-373 | 38U  | 1800mm | 800mm | IP55 | 1    |    |
| 21630-374 | 42U  | 2000mm | 600mm | IP55 | 1    |    |

| 物料号       | 机架高度 | 高度     | 宽度    | 防护等级 | 包装数量 | 颜色  |
|-----------|------|--------|-------|------|------|-----|
| 21630-375 | 42U  | 2000mm | 800mm | IP55 | 1    |     |
| 21630-376 | 47U  | 2200mm | 600mm | IP55 | 1    |     |
| 21630-377 | 47U  | 2200mm | 800mm | IP55 | 1    |     |
| 21630-711 | 38U  | 1800mm | 600mm | IP55 | 1    | 暗灰色 |
| 21630-712 | 38U  | 1800mm | 800mm | IP55 | 1    | 暗灰色 |
| 21630-713 | 42U  | 2000mm | 600mm | IP55 | 1    | 暗灰色 |
| 21630-714 | 42U  | 2000mm | 800mm | IP55 | 1    | 暗灰色 |
| 21630-715 | 47U  | 2200mm | 600mm | IP55 | 1    | 暗灰色 |
| 21630-716 | 47U  | 2200mm | 800mm | IP55 | 1    | 暗灰色 |

| Table 2/2 |      |      |       |                |      |
|-----------|------|------|-------|----------------|------|
| 物料号       | 颜色代码 | 完成   | 锁定类型  | 材料             | 快速发货 |
| 21630-372 |      | 粉末涂层 | 3 点锁定 | 钢, Stainless 钢 | No   |
| 21630-373 |      | 粉末涂层 | 3 点锁定 | 钢, Stainless 钢 | No   |
| 21630-374 |      | 粉末涂层 | 4 点锁定 | 钢, Stainless 钢 | No   |
| 21630-375 |      | 粉末涂层 | 4 点锁定 | 钢, Stainless 钢 | No   |
| 21630-376 |      | 粉末涂层 | 4 点锁定 | 钢, Stainless 钢 | No   |
| 21630-377 |      | 粉末涂层 | 4 点锁定 | 钢, Stainless 钢 | No   |

| 物料号       | 颜色代码     | 完成   | 锁定类型  | 材料 | 快速发货 |
|-----------|----------|------|-------|----|------|
| 21630-711 | RAL 7021 | 粉末涂层 | 3 点锁定 | 钢  | No   |
| 21630-712 | RAL 7021 | 粉末涂层 | 3 点锁定 | 钢  | No   |
| 21630-713 | RAL 7021 | 粉末涂层 | 4 点锁定 | 钢  | No   |
| 21630-714 | RAL 7021 | 粉末涂层 | 4 点锁定 | 钢  | No   |
| 21630-715 | RAL 7021 | 粉末涂层 | 4 点锁定 | 钢  | No   |
| 21630-716 | RAL 7021 | 粉末涂层 | 4 点锁定 | 钢  | No   |

其他产品详情

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

|                      |                        |                      |                                |
|----------------------|------------------------|----------------------|--------------------------------|
| <b>North America</b> | <b>Europe</b>          | <b>Asia</b>          | <b>Middle East &amp; India</b> |
| All locations        | Straubenhardt, Germany | Shanghai, China      | Dubai, United Arab             |
| +1.763.422.2661      | +49.7082.794.0         | +86.21.2412.6943     | Emirates                       |
| Chat with us:        | Betschdorf, France     | Qingdao, China       | +971.4.378.1700                |
| nvent.com/schroff    | +33.3.88.90.64.90      | +86.532.8771.6101    | Bangalore, India               |
|                      | Warsaw, Poland         | Singapore            | +91.80.6715.2001               |
|                      | +48.22.209.98.35       | +65.6768.5800        | Istanbul, Turkey               |
|                      | Assago, Italy          | Shin-Yokohama, Japan | +90.216.250.7374               |
|                      | +39.02.932.7141        | +81.45.476.0271      | Chat with us:                  |
|                      | Chat with us:          | Chat with us:        | nvent.com/schroff              |
|                      | nvent.com/schroff      | nvent.com/schroff    |                                |



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE