

Beam Clamp, M6 Rod, 16 mm Max Flange

物料号

EBC



认证



功能

Easy installation to beam flanges

One 10.5mm go-through hole allows the use of M6, M8 or M10 threaded rod, to attach any static load till 450N

Featuring three M6 threaded holes to attach electrical boxes directly to the side or bottom of the beam

产品属性

订货号: 170380

材料: 弹簧钢

完成: nVent CADDY 铠装

杆尺寸 (RS): 6

孔尺寸 (HS): 10.5 mm

法兰厚度 (FT): 16 mm Max

扭矩 (TQ): 20 N • m

静态负载: 450N

其他产品详情

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

