

nVent CADDY Pyramid ST Adjustable Strut Support



功能

Height adjustability provides effective navigation of pipe, conduit, duct and cable tray around obstructions

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Ready to use out of the box, saving installation time and labor

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Hot-dip galvanized and UV stabilized for long lasting performance

技术参数

Table 1/3

物料号	订货号	材料	完成	温度	静态负载安全系数	长度 1 (L1)
PSA16AH18	360469	Polyethylene, Polypropylene, 钢	热浸镀锌	-45 to 65 °C	3:1	406 mm


Table 2/3

物料号	订货号	长度 2 (L2)	高度 (H)	宽度 (W)	表面积	单位重量
-----	-----	-----------	--------	--------	-----	------

PSA16AH18	360469	483 mm	178 - 457 mm	203 mm	91613mm ²	3 kg
-----------	--------	--------	--------------	--------	----------------------	------

Table 3/3		
物料号	订货号	静态负载
PSA16AH18	360469	6670N

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

