

# 紧凑型轴流风扇

## Data Solutions



Compact Cooling Fans are ideal for applications where enclosure space is limited and quiet, reliable cooling is required. Engineered for 50,000 hours of continuous operation without lubrication or service.

### 工业标准

防护等级UL

### 功能

分相电容电机，具有热保护功能，可避免过早失效

动态平衡叶轮，由聚碳酸酯模压而成

配有一个护手板（另可提供额外的护手板）

提供所有安装五金件

风扇支架和额外的护手板需单独购买

Maximum operating temperature is 158 F (70 C)

4-inch fan is thermally protected and uses permanently lubricated ball bearings

6- and 10-inch fans have ball-bearing construction and split-capacitor motors

240 and 560 CFM fans have ball bearing construction and split capacitor motors

Fans have leadwires with ends stripped 1/2-inch (12-mm) or 6-foot (1.8-m) cord with polarized plug for power connections

### 技术参数

Table 1/2

物料号	订货号	气流	标称电压	高度	宽度	深度
-----	-----	----	------	----	----	----

A4AXFNPG	50429	170m³/h	115V	117mm	117mm	44mm
----------	-------	---------	------	-------	-------	------

Table 2/2						
物料号	订货号	最大电流	材料	完成	颜色	颜色代码
A4AXFNPG	50429	0.26A	低碳钢	粉末涂层	墨黑色	RAL 9005

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE