

Flexible Hoses for Varistar LHX+ 45 / RackChiller In-Row 45, QD-BSP, 4 米

Data Solutions

物料号

24630-174



The flexible hoses package for Varistar LHX+45 In-Rack or RackChiller In-Row 45 connects the cooling device to facility water system. The high quality EPDM hoses perform with excellent chemical stability with typical water and glycol based cooling media. The steel reinforcement provides extended pressure capability with rated nominal pressure 5 bar and minimum burst pressure 20 bar, while the external layer protects the hoses from mechanical stress and damages.

功能

用于连接 LHX+ 45 机架型或 RackChiller 直排式 45 与设施供水和回水系统的柔性软管

一对用于连接设施供水和回水系统的柔性软管

优质增强型 EPDM 柔性软管

额定工作压力为 5 巴, 最小爆破压力 > 20 巴

两端均包括 1" BSPP 扁平密封型旋转接头

4 米或 6 米长度可供选择

带快速断开装置, 以便于更换或重组冷却器

产品属性

产品类型: 软管

产品系列: RackChiller

长度: 4000mm

Net Weight: 9.54kg

包装数量: 1

其他产品详情

仅适用于 Varistar LHX+ 45 机架型和 RackChiller 直排式 45

需使用已预装 QD 的冷却器

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE