

# Enlogic Basic PDU

## Data Solutions



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

### 功能

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

### 技术参数

Table 1/6

| 物料号    | 产品系列    | 类型      | 产品类型 | 插座类型                                         | 插座数量 | 颜色 |
|--------|---------|---------|------|----------------------------------------------|------|----|
| EB0860 | Enlogic | 基本型 PDU | 插排   | (24) C13/C15,<br>(24)<br>C13/C15/C19/C<br>21 | 48   | 黑色 |
| EB09JA | Enlogic | 基本型 PDU | 插排   | (18) C13/C15,<br>(18)<br>C13/C15/C19/C<br>21 | 36   | 黑色 |
| EB0360 | Enlogic | 基本型 PDU | 插排   | (16) C13/C15                                 | 20   | 黑色 |

Table 2/6

| 物料号 | 开关插座 | 电缆长度 | 断路器 | 额定功率 | 断路器数量 | 中断额定值 |
|-----|------|------|-----|------|-------|-------|
|-----|------|------|-----|------|-------|-------|

|        |   |        |                       |                             |    |       |
|--------|---|--------|-----------------------|-----------------------------|----|-------|
| EB0860 | 否 | 3000mm | 20 A, 1<br>极, Hy-MagA | 17.3 kVA 北美,<br>22.1 kVA 国际 | 6  |       |
| EB09JA | 否 | 1800mm | 20 A, 1<br>极, Hy-MagA | 34.6 kVA 北美,<br>43.5 kVA 国际 | 12 |       |
| EB0360 | 否 | 3000mm | 16 A, 1<br>极, Hy-Mag  | 7.4 kVA                     | 2  | 5kAIC |

| Table 3/6 |        |      |       |    |         |                            |
|-----------|--------|------|-------|----|---------|----------------------------|
| 物料号       | 标称输出功率 | 标称电压 | 输出电压数 | 相数 | 包含通/断开关 | 电流 (降额电流)                  |
| EB0860    | 230VAC | 415V |       |    | 否       | 30 A (24 A)<br>北美, 32 A 国际 |
| EB09JA    | 230VAC | 415V | 36    |    | 否       | 60 A (48 A)<br>北美, 63 A 国际 |
| EB0360    | 230VAC | 230V | 20    | 1  | 否       | 32 A                       |

| Table 4/6 |              |      |                           |      |         |    |
|-----------|--------------|------|---------------------------|------|---------|----|
| 物料号       | 输出电压         | 机架单元 | 插头类型                      | 计量类型 | 可拆卸输入电缆 | 材料 |
| EB0860    | 208 – 230VAC | 0U   | IEC 60309<br>530P6/532P6  | 无    | 否       | 钢  |
| EB09JA    | 208 – 230VAC | 0U   | IEC 60309<br>560P6/563P6  | 无    | 否       | 钢  |
| EB0360    | 230VAC       | 0U   | IEC 60309<br>332P6 (IP44) | 无    | 否       | 钢  |

| Table 5/6 |      |        |       |      |       |      |
|-----------|------|--------|-------|------|-------|------|
| 物料号       | 完成   | 高度     | 宽度    | 深度   | 重量    | 包装数量 |
| EB0860    | 粉末涂层 | 1490mm | 56mm  | 55mm |       | 1    |
| EB09JA    | 粉末涂层 | 965mm  | 114mm | 75mm |       | 1    |
| EB0360    | 粉末涂层 | 817mm  | 52mm  | 53mm | 3.6kg | 1    |

| Table 6/6 |        |
|-----------|--------|
| 物料号       | 输入电缆长度 |

|        |      |
|--------|------|
| EB0860 | 3m   |
| EB09JA | 1.8m |
| EB0360 | 3m   |

其他产品详情

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE