

Secure Dual W-Lock Power Cord

Data Solutions



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

功能

安全的双锁电源线

IEC C14/C20 插头将锁定到任何 RackPower PDU 中

通用锁定 IEC 连接器将安全地锁定到任何标准 C14/C20 电源插座中

对于两种连接方式，都需要特定操作才能松开锁定按钮并断开电源

技术参数

Table 1/2

物料号	类型	搭配	长度	颜色	高度	输入电缆长度
EP1314024X15 0	电缆	RackPower	600mm	黑色	270mm	588m
EP1314048X12 5	电缆	RackPower	1200mm	黑色	270mm	1.176m
EP1314072X10 0	电缆	RackPower	1800mm	黑色	270mm	1.764m

物料号	类型	搭配	长度	颜色	高度	输入电缆长度
EP1314B24X15 0	电缆	RackPower	600mm	蓝色	270mm	0.588m
EP1314B48X12 5	电缆	RackPower	1200mm	蓝色	270mm	1.176m
EP1314B72X10 0	电缆	RackPower	1800mm	蓝色	270mm	1.764m
EP1314R24X15 0	电缆	RackPower	600mm	红色	270mm	0.588m
EP1314R48X12 5	电缆	RackPower	1200mm	红色	270mm	1.176m
EP1314R72X10 0	电缆	RackPower	1800mm	红色	270mm	1.764m
EP1920024X10 0	电缆	RackPower	600mm	黑色	270mm	0.588m
EP1920048X75	电缆	RackPower	1200mm	黑色	270mm	1.176m
EP1920072X50	电缆	RackPower	1800mm	黑色	270mm	1.764m
EP1920B24X10 0	电缆	RackPower	600mm	蓝色	270mm	0.588m
EP1920B48X75	电缆	RackPower	1200mm	蓝色	270mm	1.176m
EP1920B72X50	电缆	RackPower	1800mm	蓝色	270mm	1.764m
EP1920R24X10 0	电缆	RackPower	600mm	红色	270mm	0.588m

物料号	类型	搭配	长度	颜色	高度	输入电缆长度
EP1920R48X75	电缆	RackPower	1200mm	红色	270mm	1.176m
EP1920R72X50	电缆	RackPower	1800mm	红色	270mm	1.764m

Table 2/2			
物料号	包装数量	插头类型	可拆卸输入电缆
EP1314024X150	150	C13/C14	否
EP1314048X125	125	C13/C14	否
EP1314072X100	100	C13/C14	否
EP1314B24X150	150	C13/C14	否
EP1314B48X125	125	C13/C14	否
EP1314B72X100	100	C13/C14	否
EP1314R24X150	150	C13/C14	否
EP1314R48X125	125	C13/C14	否
EP1314R72X100	100	C13/C14	否
EP1920024X100	100	C19/C20	否
EP1920048X75	75	C19/C20	否
EP1920072X50	50	C19/C20	否
EP1920B24X100	100	C19/C20	否

物料号	包装数量	插头类型	可拆卸输入电缆
EP1920B48X75	75	C19/C20	否
EP1920B72X50	50	C19/C20	否
EP1920R24X100	100	C19/C20	否
EP1920R48X75	75	C19/C20	否
EP1920R72X50	50	C19/C20	否

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE