

# Telescopic Slides C-Profile for Cabinet

## Data Solutions



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

### 认证



### 功能

For mounting 84 HP wide subracks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the subrack (it is inserted into the guiding profile like a telescopic slide)

### 技术参数

材料:	铝
完成:	阳极氧化
类型:	C 形型材
产品类型:	伸缩滑轨



Table 1/1		
物料号	深度	包装数量
24562-460	500mm	2
24562-464	600mm	2
24562-461	600mm	2
24562-466	800mm	2
24562-474	800mm	2
24562-467	900mm	2
24562-468	1000mm	2
24562-472	1100mm	2
24562-473	1200mm	2

### 其他产品详情

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

### 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。





我们强大的品牌组合:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**