


Trapeze Sway Brace, Strut

Data Solutions



认证



功能

Seismically braces trapeze hangers

Retrofit ability allows for the brace to be installed after the trapeze assembly is installed

One wrench size fits all required hardware, eliminating the need to change tools

Shear-off head helps ensure correct torque and simplifies inspection

FM® Specification Tested

技术参数

Table 1/2

物料号	订货号	材料	完成	杆尺寸 (RS)	宽度 (W)	厚度 (T)
CSBR2	404567	钢	电镀锌	10, 12, 16, 20	81.3mm	3.4mm


Table 2/2						
物料号	订货号	A	B	C	D	E
CSBR2	404567	133.4mm	86.4mm	29mm	47.8mm	41.1mm

其他产品详情

Cut length for strut member is +/- 1" (25 mm) of measured length.

FM Loads					
Part Number	Brace Member	Horizontal Capacity per Installation Angle from Vertical			
		30° - 44°	45° - 59°	60° - 74°	75° - 90°
CSBR2	41 x 41 Strut Channel	4585 N	8060 N	8895 N	9920 N

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE