

进线口进线盖板密封塞，CEAS



Sealing plugs for the CEP cable entry series.

工业标准

UL94 V-0 Flammability; File No. E61997

NEMA Type 1, 12, 4x (indoor only)

CE

IP66

功能

Finish: White

Pack quantity: 25 pcs

Description: The CEAS sealing plugs make it easy to close pierced, unused holes in CEP cable entries. The geometry of the head prevents the ingress of spray water or dust and ensures an IP66 protection rating

Temperature resistance: -40°C to +120°C

Flammability: UL94 V-0

Protection: IP66

Material: Polyamide 6.6

Table 1/1						
物料号	订货号	高度	宽度	深度	产品系列	材料
CEAS02	58388	2mm	2mm	18mm	电缆管理	聚酰胺
CEAS03	58389	3mm	3mm	18mm	电缆管理	聚酰胺
CEAS04	58391	4mm	4mm	18mm	电缆管理	聚酰胺
CEAS05	58392	5mm	5mm	18mm	电缆管理	聚酰胺
CEAS06	58393	6mm	6mm	18mm	电缆管理	聚酰胺
CEAS07	58394	7mm	7mm	18mm	电缆管理	聚酰胺
CEAS09	58396	9mm	9mm	18mm	电缆管理	聚酰胺
CEAS10	58397	10mm	10mm	18mm	电缆管理	聚酰胺
CEAS11	58398	11mm	11mm	18mm	电缆管理	聚酰胺
CEAS12	58399	12mm	12mm	18mm	电缆管理	聚酰胺
CEAS13	58401	13mm	13mm	18mm	电缆管理	聚酰胺
CEAS14	58402	14mm	14mm	18mm	电缆管理	聚酰胺
CEAS15	58403	15mm	15mm	18mm	电缆管理	聚酰胺
CEAS16	58404	16mm	16mm	18mm	电缆管理	聚酰胺
CEAS17	58405	17mm	17mm	18mm	电缆管理	聚酰胺
CEAS22	58406	22mm	22mm	18mm	电缆管理	聚酰胺
CEAS08	58395	8mm	8mm	18mm	电缆管理	聚酰胺

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE