

ClimaGuard 空对水室内型热交换器



Air-to-Water Indoor Heat Exchanger removes heat from an enclosure by flowing enclosure hot air across a water-cooled exchanger core. Inside cabinet temperatures can range from 10-50 C (50-122 F) while ambient operating temperatures can range from 10-70 C (50-158 F). Includes a condensation recovery system and condensation discharge pipe. These units require an available cooled water source.

工业标准

UL/cUL Listed; Type 12; File No. SA33866

IP55/IP54 (参考产品技术数据)

EAC (230V models only)

IP55/IP54 (reference item technical data)

功能

无滤网、无制冷剂设计

电源线采用NEMA连接标准

热交换器盘管由铜管和铝片组成

自带过热保护

电磁水阀

Regulating mechanical thermostat set at 35 C (95 F), differential of 4 C (7 F)

技术参数

Table 1/1						
物料号	订货号	Δt 25°C 时的容量 W	Δt 25°C 时的容量 Btu/h	标称电压	高度	宽度
WCHE01926006		870W	2968Btu/h	230V	404mm	308mm
WCHE04926006		2200W	7506Btu/h	230V	925mm	400mm
WCHE06926006		3100W	10577Btu/h	230V	925mm	400mm
WCHE27846006		12500W	42650Btu/h	440V	2000mm	800mm
WCHE14926002	25616	6700W	22861Btu/h	230V	1101mm	501mm
WCHE14926006		6700W	22861Btu/h	230V	1101mm	501mm
WCHE27826006		12500W	42650Btu/h	230V	2000mm	800mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE