

Compact Design Led Light, TLCL



This energy efficient LED enclosure light can be mounted in many different ways, as well as directly on 19" profiles, in any enclosure, and helps when maintenance is performed in the field.

工业标准

CE

EAC

功能

Description: Lighting system with a compact design, suitable for all types of enclosures or racks. It has three possible fixing possibilities: magnetically, screw mounting with a variable distance between holes and/or snap-into 19" rack. This lamp has a very long service life (around 50000 h.) due to the use of LED technology. The body of the lighting system is made of PC-ABS. An integrated connector allows the activation of the lamp by a door switch by using the TLCS product without performing any additional wiring. The led-tube is made of PC and the colour of the light is white.

Lamp type: High Power LEDs.

Luminosity: 945 Lm.

Power consumption: 7.2 W.

Operating temperature: -20 °C to +50 °C.

Dimensions: 448 x 54.5 x 26 mm.

Connections: 2x0.75 mm² open end cable (1.5 m long), 2x0.75 mm² mini-connector for door switch use.

Approvals: CE, EAC.

Delivery: 1 light with fix mounted connection cable, integrated magnets and mounting screws.

Luminosity: 945 Lm

技术参数

材料： 塑料

完成： 纹理

Table 1/1						
物料号	高度	宽度	深度	颜色	颜色代码	交流电压
TLCL87035	26mm	448mm	54.5mm	浅灰色	RAL 7035	240V
TLCL87035-24	26mm	448mm	54.5mm	浅灰色	RAL 7035	
TLCL89005	26mm	448mm	54.5mm	墨黑色	RAL 9005	240V
TLCL89005-24	26mm	448mm	54.5mm	墨黑色	RAL 9005	

其他产品详情

100-240 V version available on request.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE