

紧凑型 LED 灯, CEL



A compact LED light specially designed for nVent HOFFMAN enclosures. Available with or without motion sensor. Simple through-wiring based on a plug-and-play system. Suitable for global use with a voltage range of 24-240V (AC/DC).

工业标准

UL 508A Component Recognized; File No. E61997

cUL Component Recognized per CSA C22.2 No. 14; File No. E61997

IP20

功能

Connection: Infeed, 2-pole. Through wiring, 2-pole

Follow-up time of the motion detector: 3 min.

Light colour: 5300 K (neutral white)

Dimensions: 396 x 33 x 40

Lamp type: LED

Power consumption: 5.1 W max.

Luminosity: 550 lm

Operating temperature: -20 ... +55 °C

Protection degree: IP20

Operating voltage: 24 - 240 V (AC/DC) (+/- 10%)

Description: A compact LED light specially designed for nVent HOFFMAN enclosures. Designed to fit 25mm mounting profile and accessory channel. May be fitted horizontally or vertically. The light allows up to 4 lights to be connected to each other in a daisy chain. Model ending with "M" includes motion sensor. Magnetic attachment as accessory.

Protection: II / III

技术参数

灯输出: 550lm
色温: 5800K
颜色: 黑色
灯类型: LED
灯光颜色: 中性白色
材料: 塑料
完成: 平滑哑光

Table 1/1						
物料号	订货号	高度	宽度	深度	包含运动传感器	标称电压
CEL550M	57265	396mm	33mm	40mm	是	230V
CEL550	57266	396mm	33mm	40mm	否	230V

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE