

Concept安装板

Concept面板比相应的 NEMA 尺寸面板更高、更宽。



功能

漆白色或导电饰面

Include a formed flange along any side that is longer than 22.20 in (564 mm)

Optional wood panels are made of 3/4-in plywood, pre-cut and pre-drilled to install on panel mounting studs in the rear of the cabinet

技术参数

Table 1/1						
物料号	订货号	高度	宽度	材料	完成	颜色
CP1212	78510	259mm	259mm	低碳钢	粉末涂层	白色
CP2020G	15051	462mm	462mm	低碳钢	镀锌	
CP2420	78570	564mm	462mm	低碳钢	粉末涂层	白色
CP2424	78580	564mm	563mm	低碳钢	粉末涂层	白色
CP2424G	26479	564mm	563mm	低碳钢	镀锌	
CP3024	78610	716mm	563mm	低碳钢	粉末涂层	白色
CP3024G	26489	716mm	563mm	低碳钢	镀锌	
CP3624G	26579	869mm	563mm	低碳钢	镀锌	
CP3624	78650	869mm	563mm	低碳钢	粉末涂层	白色
CP3630	78660	869mm	716mm	低碳钢	粉末涂层	白色
CP3630G	26589	869mm	716mm	低碳钢	镀锌	
CP4230	78680	1021mm	716mm	低碳钢	粉末涂层	白色
CP4236	78690	1021mm	868mm	低碳钢	粉末涂层	白色
CP4236G	15062	1021mm	868mm	低碳钢	镀锌	
CP4836	78710	1173mm	868mm	低碳钢	粉末涂层	白色
CP4836G	15064	1173mm	868mm	低碳钢	镀锌	
CP6036	78720	1478mm	868mm	低碳钢	粉末涂层	白色

物料号	订货号	高度	宽度	材料	完成	颜色
CP1212G	26429	259mm	259mm	低碳钢	镀锌	
CP1612	78520	361mm	259mm	低碳钢	粉末涂层	白色
CP1612G	26439	361mm	259mm	低碳钢	镀锌	
CP1616	78530	361mm	360mm	低碳钢	粉末涂层	白色
CP2016	78540	462mm	360mm	低碳钢	粉末涂层	白色
CP2016G	26459	462mm	360mm	低碳钢	镀锌	
CP2416G	15052	564mm	360mm	低碳钢	镀锌	
CP3012G	29671	716mm	259mm	低碳钢	镀锌	
CP3020G	15054	716mm	462mm	低碳钢	镀锌	
CP3030	78620	716mm	716mm	低碳钢	粉末涂层	白色
CP3636	78670	869mm	868mm	低碳钢	粉末涂层	白色
CP3636G	15058	869mm	868mm	低碳钢	镀锌	

其他产品详情

Catalog number CP4230 is used on Concept disconnect enclosures.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE