

# Door Horizontal Profiles, DHP



Mounting profiles are used to fit accessories to the door frame for easy and secure mounting of cables, ducts, etc.

## 功能

Description: Horizontal profiles with 25 mm hole pattern of 4.5 mm and 6.5 mm of diameter for the attachment and installation of equipment.

Material: 1.5 mm galvanized steel.

Pack quantity: 5 pieces with mounting accessories.

Mounting requirements: They fit directly onto the MMDP door mounting profiles. They can also be mounted vertically onto two horizontal profiles. For doors with espagnolette locking system, profiles must be cut where indicated.

技术参数

厚度: 1.5mm  
完成: 镀锌  
材料: 低碳钢

| Table 1/1 |        |      |       |      |      |      |
|-----------|--------|------|-------|------|------|------|
| 物料号       | 订货号    | 高度   | 宽度    | 深度   | 包装数量 | 快速发货 |
| DHP040    | DHP040 | 25mm | 348mm | 12mm | 5    | No   |
| DHP050    | DHP050 | 25mm | 448mm | 12mm | 5    | No   |
| DHP030    | DHP030 | 25mm | 248mm | 12mm | 5    | No   |
| DHP060    | DHP060 | 25mm | 548mm | 12mm | 5    | No   |
| DHP080    | DHP080 | 25mm | 748mm | 12mm | 5    | No   |

其他产品详情

Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**