

弯头 90 度嵌入式铰链盖



Lay-in Hinged-Cover 90-Degree Elbows are used for right-angle wireway installations. Because sections of lay-in wireway can be mounted with covers oriented in any direction, three different 90-degree elbows are available. Proper selection allows the user to maintain the same access and thereby preserve the lay-in feature for right-angle installations.

工业标准

通过加拿大标准协会认证

功能

嵌入式铰链盖 90 度弯头适用于直角线槽安装

嵌入式线槽的节段可安装在任何朝向的盖子上，因此可使用三种不同的 90 度弯头

正确的选择让用户能够保持同一入口，从而保留直角安装的嵌入特性

技术参数

颜色代码: ANSI 61

完成: 镀锌; 粉末涂层

颜色: 灰色

材料: 低碳钢

Table 1/1						
物料号	订货号	类型	高度	宽度	厚度	密封板类型
F126LE9B	18820	弯管	305mm	152mm	1.9mm	扁平
F22LE9A	18110	弯管	64mm	64mm	1.9mm	扁平
F22LE9B	18120	弯管	64mm	64mm	1.9mm	扁平
F22LE9C	18130	弯管	64mm	64mm	1.9mm	扁平
F44LE9A	18340	弯管	102mm	102mm	1.9mm	扁平
F44LE9B	18350	弯管	102mm	102mm	1.9mm	扁平
F44LE9C	18360	弯管	102mm	102mm	1.9mm	扁平
F66LE9A	18580	弯管	152mm	152mm	1.9mm	扁平
F66LE9B	18590	弯管	152mm	152mm	1.9mm	扁平
F66LE9C	18600	弯管	152mm	152mm	1.9mm	扁平

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE