

Electronic Thermostat / Hygrostat, ETF300



This adjustable thermostat and hygrostat, ETF300 and ETF300120, with either a normally open (NO) or normally closed (NC) contact, manages both relative humidity and temperature. It is used to control installed devices, such as a fan heater, to turn on or off at the required humidity and temperature levels, that are set by the user. The result is elimination of water condensation at a reduced operational cost.

工业标准

cULus_UL

CE

EAC

功能

Connection: Pole terminal for 2.5 mm².

Service life: 50,000 cycles.

Setting range for ETF300: 0 °C to +60 °C and 40 to 90% R.H.

Setting range for ETF300120: +32 °F to +140 °F and 40 to 90% R.H.

Operating temperature: -20 °C to +60 °C.

Pack quantity: 1 piece.

Switch capacity: 240 V AC, 8(3) A. 120 V AC, 8(3) A. 24 V DC, 4 A. Value in brackets for inductive load.

Description: Electronic hygrostat-thermostat monitors the relative humidity and the temperature independently of each other, and it manages heaters and filter fans to prevent condensation and corrosion inside the enclosure.

Mounting clip for 35 mm DIN rail (EN 60715).

Approvals: CE, EAC, cULus_UL Listed.

Protection: IP 20.

Material: Plastic according to UL94 V-0.

Finish: RAL 7035.

The installed devices, such as fan heaters, automatically turn on or off when they are required, which reduces the operational cost of the control panel.

Customers can adjust the required humidity and temperature, which means it can be installed in any enclosure, and is not dependant on the other installed components or equipment

The reliable thermostat and hygrostat manages both the relative humidity and temperature within the enclosure, preventing water condensation from occurring.

Frequency (Hz): 50/60

技术参数

Table 1/1						
物料号	高度	宽度	深度	材料	完成	颜色
ETF300120	83mm	59mm	45mm	塑料	平滑	浅灰色
ETF300	83mm	59mm	45mm	塑料	平滑	浅灰色

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE