

Continuous Hinge Enclosure with Clamps Type 4, 10x8x4, Gray, Mild Steel

物料号

A1008CHNF



A continuous hinge combined with stainless steel clamps on three sides provide environmental protection and security in indoor or outdoor applications.

工业标准

UL 50, 50E Listed; Type 4, 12, 13; File No. E27567

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E27567

UL 508A Listed; Type 4, 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 13; File No. E61997

NEMA/EEMAC Type 4, 12, 13

CSA, File No. 42184: Type 4 and 12

IEC 60529, IP66

功能

Seams continuously welded and ground smooth

Stainless steel screw-down clamps on three sides of door

Continuous hinge

Stainless steel hinge pin

Oil-resistant gasket

Weldnuts provided for mounting optional panels and terminal block kits in size 6.00 x 4.00 in. (152 x 102 mm) and larger

Bonding provision on door

External wall-mounting brackets for easy installation

产品属性

订货号: 55730

高度: 254mm

宽度: 203mm

深度: 102mm

材料: 低碳钢

完成: 粉末涂层

颜色: 灰色

颜色代码: ANSI 61

厚度: 1.9mm

安装: 273 x 152mm

整体尺寸: 292 x 227mm

其他产品详情

Catalog numbers ending in "S" are hinged on short side.

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE