

Partial door, 150x600, Mild steel, 3mm double bit lock, IP44

物料号

DP01506R5



Partial doors allow for many different, easily accessible configurations of separate compartments, within the enclosure.

功能

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CHDK. Equipped with double-bit 3 mm lock (1 lock up to 400 mm, over 400 mm height 2 locks).

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44.

Pack quantity: 1 door with hinges, locks and mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

产品属性

高度: 150mm

宽度: 600mm

深度: 17mm

外壳材料: 低碳钢

产品系列: 独立

材料: 低碳钢

完成: 粉末涂层

颜色: 浅灰色

颜色代码: RAL 7035

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE