

ProLine G2 Vented Plinth Base Cover, 1600, Steel, Black

物料号

P2APBVC16



The Vented Plinth Base Covers replace the traditional solid plinth base covers that mount width-wise across the front and rear of the enclosure. Vented covers allow air to enter the enclosure from below, and are used in conjunction with the Vented Gland Plate.

功能

包含安装硬件

产品属性

订货号: 36153

框架类型: 双托架

完成: 粉末涂层

适配框架宽度: 1600mm

颜色: 墨黑色

颜色代码: RAL 9005

材料: 低碳钢

厚度: 1.52mm

其他产品详情

Please note that a standard 100mm Solid Plinth Base must be ordered separately, as Vented Plinth Base Covers are replacements for the front and rear covers only. Vented Gland Plate also sold separately, but required for successful air passage.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE