

前/后底座，PFS



This stainless steel plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

功能

Description: Front and rear plinth sections. For cabling without any restrictions and in accordance with the VDE 0113 standard. The plinth consists of four corner pieces with removable front covers. The side panels PSS are to be ordered separately. Produced in 100 mm and 200 mm heights. 200 mm high plinths are delivered with a rear cover for cabling that consists of two removable panels 100 mm high. The front cover is a one piece panel of 200 mm high. All panels have double returns on each panel for added strength.

Material: AISI 304 / AISI 316L pre-grained stainless steel. Corners 2 mm and panels 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1x front plinth and 1x rear plinth with mounting accessories.

Mounting requirements: Add the side panels PSS for a complete plinth.

技术参数

厚度: 1.5mm
完成: 拉丝

Table 1/1						
物料号	订货号	高度	宽度	深度	外壳材料	产品系列
PFS1120	PFS1120	100mm	1200mm	60mm	低碳钢	独立
PFS2120		200mm	1200mm	60mm	低碳钢	独立
PFS1080	PFS1080	100mm	800mm	60mm	低碳钢	独立
PFS2080		200mm	800mm	60mm	低碳钢	独立
PFS1060	PFS1060	100mm	600mm	60mm	低碳钢	独立
PFS2060		200mm	600mm	60mm	低碳钢	独立
PFS1100		100mm	1000mm	60mm	低碳钢	独立
PFS2100		200mm	1000mm	60mm	低碳钢	独立
PFS1060-316		100mm	600mm	60mm	低碳钢	独立
PFS1080-316		100mm	800mm	60mm	低碳钢	独立
PFS1100-316		100mm	1000mm	60mm	低碳钢	独立
PFS1120-316		100mm	1200mm	60mm	低碳钢	独立
PFS2060-316		200mm	600mm	60mm	低碳钢	独立
PFS2080-316		200mm	800mm	60mm	低碳钢	独立
PFS2100-316		200mm	1000mm	60mm	低碳钢	独立

物料号	订货号	高度	宽度	深度	外壳材料	产品系列
PFS2120-316		200mm	1200mm	60mm	低碳钢	独立

其他产品详情

For enclosures 1600 mm wide use 2 x 800 mm wide plinth.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE