

密封条套件



Gasket kits are ideal to replace damaged or worn foam-in-place or strip enclosure gaskets. Available in either EPDM or silicone material, these gasket kits allows replacement of current gasket as well as provides a solution to upgrade enclosure gasket for harsh applications. Kits offered with different sized gaskets is suitable to be used on either Wall-Mount or Free-Stand/Floor-Mount Enclosures.

工业标准

UL 508A Component Recognized; Type 4, 4x, 12; File No. E61997
cUL Component Recognized per CSA C22.2 No 94; File No. E61997

适用于 HOFFMAN 机柜 Type 4、4X 和 12 等级的门、盖和进线盖板密封的现场安装。

功能

安装在机柜门内，为机柜的外壳和门提供密封屏障

EPDM 密封条套件是更换损坏或磨损的机柜密封条的理想选择

硅胶密封条可提供安全密封，在极端温度下防水防尘

硅胶密封条可用于升级恶劣应用的当前密封条，或替换当前硅胶密封条

条状密封条可现场安装，附带密封剂和说明书

每个套件包括一卷 20 英尺（6 米）长的条状密封条

Gaskets available in .63-in. (16-mm) wide for Wall-Mount Enclosures

Gaskets available in 1.00-in. (25-mm) wide for Free-Stand and Floor-Mount Enclosures

技术参数

Table 1/1						
物料号	订货号	长度	宽度	材料	完成	颜色
GSKTKITS375	29154	6.1m	25mm	硅树脂	平滑哑光	黑色

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE