

# Ground Mounted Plinth, PGM



Cables can be easily routed through the ground plinth, which is mounted underground, allowing cables to be channelled and therefore, wired more quickly.

## 功能

Description: Ground mounted plinth 1000 mm height. Excavation depth: 700-950 mm.

Material: 2 mm galvanized steel.

Finish: RAL 7035 polyester powder coated.

Pack quantity: 1 kit of ground mounted plinth.

技术参数

厚度: 2mm

完成: 镀锌

材料: 镀锌钢

颜色: 浅灰色

颜色代码: RAL 7035

Table 1/1						
物料号	高度	宽度	深度	外壳材料	产品系列	快速发货
PGM10064	1000mm	600mm	400mm	铝	独立	No
PGM10066	1000mm	600mm	600mm	铝	独立	No
PGM10084	1000mm	800mm	400mm	铝	独立	No
PGM10086	1000mm	800mm	600mm	铝	独立	No
PGM10124	1000mm	1200mm	400mm	铝	独立	No
PGM10126	1000mm	1200mm	600mm	铝	独立	No
PGM10184	1000mm	1800mm	400mm	铝	独立	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**