


重型外开式机架框



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

功能

弹簧支承枢轴柱让安装变得简单

配有铰链、两个四分之一旋转锁杆和安装五金件

安装孔适合英式或公制锁紧螺母（单独订购）

外开式机架框架组件带安装支撑

可选可旋转 170 度的铰链

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

RAL 7035 textured light-gray polyester powder paint

技术参数

厚度: 2.66mm
颜色: 浅灰色
完成: 粉末涂层
颜色代码: RAL 7035

Table 1/1					
物料号	订货号	材料	适配框架宽度	机架单元	快速发货
PSF76	91220	低碳钢	600mm	10U	No
PSF146	99640	低碳钢	600mm	25U	No
PSF148	99740	低碳钢	800mm	25U	No
PSF78	91240	低碳钢	800mm	10U	No
PSF168	99750	低碳钢	800mm	30U	No
PSF186	99660	低碳钢	600mm	34U	No
PSF188	99760	低碳钢	800mm	34U	No
PSF206	99670	低碳钢	600mm	39U	No
PSF77	91230	低碳钢	700mm	10U	No
PSF207	99720	低碳钢	700mm	39U	No
PSF208	99770	低碳钢	800mm	39U	No
PSF226	99680	低碳钢	600mm	43U	No
PSF227	99730	低碳钢	700mm	43U	No
PSF228	99780	低碳钢	800mm	43U	No
PSF166	99650	低碳钢	600mm	30U	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE