

Hol-Sealers 非金属孔密封件

Designed for use in corrosive environments to seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water. These hole seals are suitable for sealing enclosure openings in industries such as petroleum and chemical processing, wastewater processing, pulp and paper, outdoor monitoring and any other industry exposed to harsh environments.

工业标准

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997

CSA 文件编号 42186; Type 3R、4、12、13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66



功能

非金属结构提供卓越的耐腐蚀性，可在恶劣环境中实现可靠性

紫外线稳定；适用于阳光直射（避免玻璃纤维与玻璃纤维相关联）

对多种化学物质具有化学抗性

经久耐用，抗冲击，抗开裂

不锈钢的经济高效替代品

易于安装；无需工具

螺纹和螺母由非玻璃填充聚酯构成

包括耐油密封条

Innovative 3-in-1 self-centering design reduces inventory requirements; 3 models cover 9 common industry cutouts ranging from 1/2 inch (13mm) to 2-1/2 inch (64mm)

Sold in quantities of 2 per catalog number

Polyester material has a UL 94 rating of 5VA

技术参数

Table 1/1						
物料号	订货号	孔直径	材料	完成	颜色	颜色代码
ASPB05075NM	16307	33mm max	聚酯	纹理	浅灰色	RAL 7035
AS150200250NM	16311	80mm max	聚酯	纹理	浅灰色	RAL 7035
ASPB100125NM	16308	49mm max	聚酯	纹理	浅灰色	RAL 7035

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE