

Inner Doors, ADIS



Displays and indicators can be mounted, on a surface within the enclosure while covering other components, and preventing unauthorized access.

功能

将安装在壁挂式机柜内的平板型门

额外安装表面提供两层通道

Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening (Machining is required). Double-bit 3 mm lock, 800 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm, adjustable depth position with AMG accessory. Workable area: H-55, W-108. 19" version available on request.

Material: Door 1.5 mm AISI 304 stainless steel and vertical top and bottom profiles 2 mm, AISI 304 stainless steel.

Protection: IP 2XC.

Finish: 400 pre-grained stainless steel.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

技术参数

完成： 拉丝
材料： 不锈钢 304

Table 1/1						
物料号	高度	宽度	深度	门尺寸	门锁数量	外壳材料
ADIS04030	400mm	300mm	15mm	345 x 192mm	1	低碳钢
ADIS05040	445mm	292mm	15mm	445 x 292mm	1	低碳钢
ADIS05050	445mm	392mm	15mm	445 x 392mm	1	低碳钢
ADIS06040	545mm	292mm	15mm	545 x 292mm	1	低碳钢
ADIS06060	545mm	492mm	15mm	545 x 492mm	1	低碳钢
ADIS08060	745mm	492mm	15mm	745 x 492mm	2	低碳钢
ADIS10080	945mm	692mm	15mm	945 x 692mm	2	低碳钢
ADIS12080	1145mm	692mm	15mm	1145 x 692mm	2	低碳钢

其他产品详情

产品

To order 19"version, please add I19 to the catalogue no, e.g. ADIS04030I19. Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE