

Modular Chassis, AC



DIN-rail components can be mounted quickly and easily to this chassis, both at the panel builders and in the field.

功能

Description: Used for easy mounting of DIN-rail components with a maximum height of 68 mm. Distance between rows 125 mm. If required, the standard enclosure door can be replaced with a glazed door. Usable depth between front cover and external door: 35 mm. In stainless steel enclosure machining is required.

Material: DIN-rails PP0735 made of 1.2 mm galvanized steel, vertical profiles 1.5 mm mild steel, and front cover 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: Slotted front panel, two vertical profiles, top and bottom blank panels, one DIN-rail per row, and mounting accessories.

Mounting requirements: To be assembled on MAS and ASR enclosures.

技术参数

厚度: 1.2mm
颜色: 浅灰色
材料: 低碳钢
完成: 粉末涂层
颜色代码: RAL 7035

Table 1/1						
物料号	订货号	高度	宽度	深度	外壳材料	模块数量
AC03025R5	AC03025R5	300mm	250mm	98mm	低碳钢	16
AC04030R5	AC04030R5	400mm	300mm	98mm	低碳钢	33
AC05040R5	AC05040R5	500mm	400mm	98mm	低碳钢	48
AC06040R5	AC06040R5	600mm	400mm	98mm	低碳钢	64
AC06060R5	AC06060R5	600mm	600mm	98mm	低碳钢	108
AC07050R5	AC07050R5	700mm	500mm	98mm	低碳钢	110
AC08060R5	AC08060R5	800mm	600mm	98mm	低碳钢	162
AC10060R5	AC10060R5	1000mm	600mm	98mm	低碳钢	189
AC10080R5	AC10080R5	1000mm	800mm	98mm	低碳钢	266

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE