

Partial Doors For Floor Standing Enclosures, DP



Partial doors allow for many different, easily accessible configurations of separate compartments, within the enclosure.

功能

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CHDK. Equipped with double-bit 3 mm lock (1 lock up to 400 mm, over 400 mm height 2 locks).

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44.

Pack quantity: 1 door with hinges, locks and mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

技术参数

颜色: 浅灰色
材料: 低碳钢
完成: 粉末涂层
颜色代码: RAL 7035

Table 1/1						
物料号	高度	宽度	深度	外壳材料	产品系列	快速发货
DP01504R5	150mm	400mm	17mm	低碳钢	独立	No
DP01506R5	150mm	600mm	17mm	低碳钢	独立	No
DP01508R5	150mm	800mm	17mm	低碳钢	独立	No
DP02004R5	200mm	400mm	17mm	低碳钢	独立	No
DP02006R5	200mm	600mm	17mm	低碳钢	独立	No
DP02008R5	200mm	800mm	17mm	低碳钢	独立	No
DP02504R5	250mm	400mm	17mm	低碳钢	独立	No
DP02506R5	250mm	600mm	17mm	低碳钢	独立	No
DP02508R5	250mm	800mm	17mm	低碳钢	独立	No
DP03004R5	300mm	400mm	17mm	低碳钢	独立	No
DP03006R5	300mm	600mm	17mm	低碳钢	独立	No
DP03008R5	300mm	800mm	17mm	低碳钢	独立	No
DP04004R5	400mm	400mm	17mm	低碳钢	独立	No
DP04006R5	400mm	600mm	17mm	低碳钢	独立	No
DP04008R5	400mm	800mm	17mm	低碳钢	独立	No

物料号	高度	宽度	深度	外壳材料	产品系列	快速发货
DP05004R5	500mm	400mm	17mm	低碳钢	独立	No
DP05006R5	500mm	600mm	17mm	低碳钢	独立	No
DP05008R5	500mm	800mm	17mm	低碳钢	独立	No
DP06004R5	600mm	400mm	17mm	低碳钢	独立	No
DP06006R5	600mm	600mm	17mm	低碳钢	独立	No
DP06008R5	600mm	800mm	17mm	低碳钢	独立	No
DP08006R5	800mm	600mm	17mm	低碳钢	独立	No
DP08008R5	800mm	800mm	17mm	低碳钢	独立	No
DP10006R5	1000mm	600mm	17mm	低碳钢	独立	No
DP10008R5	1000mm	800mm	17mm	低碳钢	独立	No
DP12006R5	1200mm	600mm	17mm	低碳钢	独立	No
DP12008R5	1200mm	800mm	17mm	低碳钢	独立	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE