

Plastic Cable Glands For Wall Mounted Enclosures, CPG



The compression of each cable fitted in this cable gland can be adjusted, and is secured using a locking nut, which provides strain relief as well as a high ingress protection.

功能

Description: Traditional cable fittings. Known for excellent strain relief even while providing a high protection class. Plastic lock nuts for fixation are included in the delivery.

Material: Fitting body made of polyamide PA6, and sealing made of neoprene.

Temperature resistance: -20°C to +100°C.

Flammability: V-2 according to UL94.

Finish: RAL 7035.

Protection: IP 66

技术参数

颜色: 浅灰色

材料: 聚酰胺 6; 氯丁橡胶

颜色代码: RAL 7035

完成: 平滑

Table 1/1						
物料号	高度	宽度	深度	外壳材料	产品系列	螺纹尺寸
CPG12	31mm	15mm	17mm	低碳钢	壁挂式安装	M12 x 1.5
CPG16	40mm	22mm	24mm	低碳钢	壁挂式安装	M16 x 1.5
CPG20	40mm	24mm	26mm	低碳钢	壁挂式安装	M20 x 1.5
CPG25	46mm	33mm	35mm	低碳钢	壁挂式安装	M25 x 1.5
CPG32	56mm	42mm	44mm	低碳钢	壁挂式安装	M32 x 1.5
CPG40	68mm	53mm	55mm	低碳钢	壁挂式安装	M40 x 1.5
CPG50	71mm	60mm	62mm	低碳钢	壁挂式安装	M50 x 1.5
CPG63	71mm	65mm	67mm	低碳钢	壁挂式安装	M63 x 1.5

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE