

Plinth 底座, MSVS



The plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

功能

Description: Four U-section side pieces fixed by screws to the corner sections. Plinth height 100 mm. Machining is required.

Material: 2 mm AISI 304 / AISI 316L pre-grained stainless steel.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 plinth with mounting material.

技术参数

厚度: 2mm
完成: 拉丝

Table 1/1						
物料号	订货号	高度	宽度	深度	材料	外壳材料
MSVS1103	MSVS1103	100mm	1000mm	300mm	不锈钢 304	低碳钢
MSVS1103-316	MSVS1103-316	100mm	1000mm	300mm	不锈钢 316L	低碳钢
MSVS1123	MSVS1123	100mm	1200mm	300mm	不锈钢 304	低碳钢
MSVS1123-316	MSVS1123-316	100mm	1200mm	300mm	不锈钢 316L	低碳钢
MSVS1124	MSVS1124	100mm	1200mm	400mm	不锈钢 304	低碳钢
MSVS1124-316	MSVS1124-316	100mm	1200mm	400mm	不锈钢 316L	低碳钢
MSVS1063	MSVS1063	100mm	600mm	300mm	不锈钢 304	低碳钢
MSVS1063-316	MSVS1063-316	100mm	600mm	300mm	不锈钢 316L	低碳钢
MSVS1083	MSVS1083	100mm	800mm	300mm	不锈钢 304	低碳钢
MSVS1083-316	MSVS1083-316	100mm	800mm	300mm	不锈钢 316L	低碳钢
MSVS1084	MSVS1084	100mm	800mm	400mm	不锈钢 304	低碳钢
MSVS1084-316	MSVS1084-316	100mm	800mm	400mm	不锈钢 316L	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE