

Power Socket With Integrated Fuse, LPS



Easy to mount power sockets, to be mounted on a DIN rail, for use when external equipment needs to be plugged in.

工业标准

cULus_UL listed

CE

GOST

功能

Description: DIN rail mounted electrical socket. Pressure clamp connection for easy and quick wiring.

Dimensions: 92 mm x 62 mm x 48 mm.

Connection: 3 pressure clamps for stranded and rigid wire 0.5-2.5 mm². Integrated fuse 6,3A 5x20 mm.

Finish: Light grey.

Material: Plastic UL 94 V-0.

Pack quantity: 1 piece.

技术参数

颜色: 浅灰色

材料: 塑料

颜色代码: RAL 7035

完成: 平滑

Table 1/1						
物料号	高度	宽度	深度	插座类型	重量	快速发货
LPS10	92mm	62mm	48mm	SCHUKO	120kg	No
LPS10UK	92mm	62mm	48mm	G 型	120kg	No
LPS10CH	92mm	62mm	48mm	Switzerland	120kg	No
LPS10USA	92mm	62mm	48mm	A 型	120kg	No
LPS10FR	92mm	62mm	48mm	F 型	120kg	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE