

Rain Hood, URH



A polyester rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

功能

Description: Extra protection for outdoor use. Ventilation holes can be drilled in the top of the enclosure. When mounted, the enclosure's degree of protection is IP 44.

Material: Glass fibre reinforced polyester.

Finish: RAL 7035.

Delivery: 1 piece with mounting accessories.

Mounting requirements: Rain hoods require special wall mounting brackets UWB02. Four fixing points for securing the rain hood are marked off in the top panel. The rain hood cannot be used when the enclosures are joined, some combinations are available on request. Machining is required.

Rain hoods are not compatible with combined enclosures

If the enclosure is to be mounted to a wall, the wall mounting brackets, UWB02, must be used

When the rain hood is mounted, the enclosure's protection degree is IP44

Extra protection for outdoor use

Ventilation holes can be drilled in the top of the enclosure

Glass fibre reinforced polyester

1 piece with mounting accessories

Rain hoods require special wall mounting brackets UWB02

Four fixing points for securing the rain hood are marked off in the top panel

The rain hood cannot be used when the enclosures are joined, some combinations are available on request. Machining is required

Package quantity: 1 with mounting hardware

技术参数

颜色: 浅灰色

材料: 聚酯

颜色代码: RAL 7035

完成: 平滑

Table 1/1						
物料号	高度	宽度	深度	外壳材料	产品系列	快速发货
URH10032	53mm	1040mm	340mm	聚酯	壁挂式安装	No
URH7532	53mm	790mm	340mm	聚酯	壁挂式安装	No
URH5032	53mm	540mm	340mm	聚酯	壁挂式安装	No
URH12532	53mm	1290mm	340mm	聚酯	壁挂式安装	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE