

Roof mount Air-to-Water Heat Exchanger, BIT



Industrial roof mount air-to-water heat exchangers remove heat from enclosures by using chilled fluid, which offers a reliable and low maintenance enclosure cooling option.

认证



功能

Finish: RAL 7035 for the galvanized steel versions

Internal temperature range: +20 °C to +60 °C

Ambient temperature range: +1 °C to +70 °C

Pack quantity: 1

技术参数

电缆长度: 3m

额定频率: 50 – 60Hz

材料: 镀锌钢

防护等级: IP55

Table 1/1						
物料号	Δt 25°C 时的容量 W	标称电压	高度	宽度	深度	快速发货
BIT25BX0B	2500W	230V	270mm	400mm	540mm	No
BIT25CX0B	2500W	115V	270mm	400mm	540mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE