

Stainless Steel Plain Door, DNSS



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

功能

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMKS (hinges, rod catches) to be ordered separately. Allows all the options of the locking programme and 180° hinges. Compatible with combinable and compact stainless steel enclosure ranges.

Material: 2 mm AISI 304 stainless steel plate / AISI 316L (on request).

Maximum load: 800 N.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMKS if no door was fitted previously.

技术参数

厚度: 2mm
完成: 拉丝
材料: 不锈钢 304

Table 1/1						
物料号	高度	宽度	深度	门类型	外壳材料	产品系列
DNSS1212L	1200mm	600mm	17mm	左门	低碳钢	独立
DNSS1212R	1200mm	600mm	17mm	右门	低碳钢	独立
DNSS1408	1400mm	800mm	17mm	单门	低碳钢	独立
DNSS1606	1600mm	600mm	17mm	单门	低碳钢	独立
DNSS1608	1600mm	800mm	17mm	单门	低碳钢	独立
DNSS1610	1600mm	1000mm	17mm	单门	低碳钢	独立
DNSS1612L	1600mm	600mm	17mm	左门	低碳钢	独立
DNSS1612R	1600mm	600mm	17mm	右门	低碳钢	独立
DNSS1806	1800mm	600mm	17mm	单门	低碳钢	独立
DNSS1808	1800mm	800mm	17mm	单门	低碳钢	独立
DNSS1810	1800mm	1000mm	17mm	单门	低碳钢	独立
DNSS1810L	1800mm	500mm	17mm	左门	低碳钢	独立
DNSS1810R	1800mm	500mm	17mm	右门	低碳钢	独立
DNSS1812L	1800mm	600mm	17mm	左门	低碳钢	独立
DNSS1812R	1800mm	600mm	17mm	右门	低碳钢	独立

物料号	高度	宽度	深度	门类型	外壳材料	产品系列
DNSS1816L	1800mm	800mm	17mm	左门	低碳钢	独立
DNSS1816R	1800mm	800mm	17mm	右门	低碳钢	独立
DNSS2006	2000mm	600mm	17mm	单门	低碳钢	独立
DNSS2008	2000mm	800mm	17mm	单门	低碳钢	独立
DNSS2010	2000mm	1000mm	17mm	单门	低碳钢	独立
DNSS2012L	2000mm	600mm	17mm	左门	低碳钢	独立
DNSS2012R	2000mm	600mm	17mm	右门	低碳钢	独立
DNSS2016L	2000mm	800mm	17mm	左门	低碳钢	独立
DNSS2016R	2000mm	800mm	17mm	右门	低碳钢	独立

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE