

Syspend 281-Max 垂直运动基座管



Syspend 281-Max Vertical Motion Pedestal Tube is a vertical adjustable tube with a lift range of 250mm, allowing enclosure to be positioned at the optimal viewing height for different operators. The 48-mm Round Tube Flange Coupling (S2MFC48) and Adapter (S2MA48) is required for attachment to HMI enclosures with a 60 x 60-mm hole pattern (i.e. Syspend Aluminum HMI and Concept HMI). The weight of the coupling, adapter plate, enclosure and internal components must be factored into the load when selecting a tube.

功能

可以使用锁紧把手将高度固定在任何位置

线缆与管内的气弹簧隔离

管内线缆的内部应力消除

可连接到小底座、垂直壁挂接头、墙壁法兰、旋转底座、弯头或旋转弯头

不得将管倒置以在机柜上进行架空安装

Adjustable from 1130 mm (44.49 in.) to 1380 mm (54.33 in.) with internal gas springs

Four models support loads ranging from 11 to 77 lb. (4.9 to 34.9 kg)

技术参数

材料： 铝
完成： 阳极氧化

Table 1/1						
物料号	订货号	高度	宽度	深度	厚度	最大 L
S2M10VP57	18835	1380mm	70mm	90mm	6mm	350mm
S2M10VP77	18836	1380mm	70mm	90mm	6mm	350mm
S2M10VP22	18833	1380mm	70mm	90mm	6mm	350mm
S2M10VP37	18834	1380mm	70mm	90mm	6mm	350mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE