

# Top And Bottom Panels For Floor Standing Enclosures, DPC



Both the enclosure's aesthetics and IP-rating are maintained when a complete set of doors and panels are mounted.

## 功能

Description: Required to cover the remaining space at the top and bottom. Used in combination with horizontal dividers CDH/CDHK, partial doors DP, partial panels DPP and cable space door DPA.

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44. For IP 21 delivered without gasket.

Mounting requirements: DPC covers 200 mm in height of the enclosure. So for a 2000 mm high enclosure when DPC is used, there is 1800 mm space left for partial doors/panels.

Pack quantity: Top and bottom panel with mounting accessories.

技术参数

厚度: 1.75mm

颜色: 浅灰色

材料: 低碳钢

完成: 粉末涂层

颜色代码: RAL 7035

Table 1/1						
物料号	高度	宽度	深度	外壳材料	产品系列	快速发货
DPC0714R5	104mm	400mm	17mm	低碳钢	独立	No
DPC0716R5	104mm	600mm	17mm	低碳钢	独立	No
DPC0718R5	104mm	800mm	17mm	低碳钢	独立	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE