

Universal Busbar Support, WO60



Busbar support that enables creation of a safe and easy to use system with 60 mm distance between busbar systems.

工业标准

GL

DNV-GL

功能

Description: Universal busbar support 3/4-Pole with internal screw holes, delivered without end cover.

Rated voltage: 690 V

Rated frequency: 50/60 Hz

Rated isolation voltage U_i : 1000 V

Rated surge voltage U_{imp} : 8 kV

Approvals: GL, DNV GL

Rated frequency: 50/60 Hz

Rated isolation voltage U_i : 1000 V

Rated surge voltage U_{imp} : 8 kV

技术参数

Table 1/1						
物料号	高度	宽度	深度	外壳材料	产品系列	材料
01485	20mm	242mm	51mm	塑料, 钢	IEC 通用附件	塑料, 钢
01495	20mm	191mm	50mm	塑料, 钢	IEC 通用附件	塑料, 钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE