

## Ventilated Top And Bottom Panels For Floor Standing Enclosures, DPCV



Both the enclosure's aesthetics and IP-rating are maintained when a complete set of doors and panels are mounted. The ventilation panels also provide natural ventilation.

## 功能

Description: Required to cover the remaining space at the top and bottom. With ventilation slots for added heat dissipation in switchgear enclosures. Used in combination with horizontal dividers CDH/CDHK

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 20.

Mounting requirements: DPCV covers 200 mm in height of the enclosure. So for a 2000 mm high enclosure when DPCV is used, there is 1800 mm space left for partial doors/panels.

Pack quantity: 2 panels with mounting accessories.

## 技术参数

厚度: 1.75mm

颜色: 浅灰色

材料: 低碳钢

完成: 粉末涂层

颜色代码: RAL 7035

Table 1/1						
物料号	高度	宽度	深度	高度 [1]	高度 [2]	外壳材料
DPCV0716R5	104mm	600mm	17mm	70mm	100mm	低碳钢
DPCV0714R5	104mm	400mm	17mm	70mm	100mm	低碳钢
DPCV0718R5	104mm	800mm	17mm	70mm	100mm	低碳钢

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书,或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告,可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE