

Window Door, ADC



可在门关闭的情况下查看电气组件，避免频繁开关机柜。

功能

Description: To replace the standard door, it provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s).

Material: 1.2 mm mild steel / 1.5 mm for enclosures with a height or width of 500 mm or greater / 2 mm for enclosures with a height or width of 800 mm or greater and 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, 13, IK 07.

Pack quantity: 1 door.

技术参数

颜色: 浅灰色
材料: 低碳钢
完成: 粉末涂层
颜色代码: RAL 7035

Table 1/1						
物料号	订货号	高度	宽度	深度	厚度	门锁数量
ADC03025R5	ADC03025R5	300mm	250mm	15mm	1.2mm	1
ADC03030R5	ADC03030R5	300mm	300mm	15mm	1.2mm	1
ADC04030R5	ADC04030R5	400mm	300mm	15mm	1.2mm	1
ADC04040R5	ADC04040R5	400mm	400mm	15mm	1.2mm	1
ADC05030R5	ADC05030R5	500mm	300mm	15mm	1.5mm	1
ADC05040R5	ADC05040R5	500mm	400mm	15mm	1.5mm	1
ADC06040R5	ADC06040R5	600mm	400mm	15mm	1.5mm	2
ADC06050R5	ADC06050R5	600mm	500mm	15mm	1.5mm	2
ADC06060R5	ADC06060R5	600mm	600mm	15mm	1.5mm	2
ADC07050R5	ADC07050R5	700mm	500mm	15mm	1.5mm	2
ADC08060R5	ADC08060R5	800mm	600mm	15mm	2mm	2
ADC10060R5	ADC10060R5	1000mm	600mm	15mm	2mm	1
ADC10080R5	ADC10080R5	1000mm	800mm	15mm	2mm	1
ADC12060R5	ADC12060R5	1200mm	600mm	15mm	2mm	1
ADC12080R5	ADC12080R5	1200mm	800mm	15mm	2mm	1

* 3 point espagnolette locking. Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE