

A2 Standard Coupler, Coated



Coated reinforcing bar is used in place of plain reinforcing bars to protect against corrosion. Typical applications include bridges, parking structures, pavement, marine structures and repair work. nVent LENTON couplers and mechanical anchors are available in multiple coatings to meet specific job requirements.

认证



功能

Designed to splice the same diameter bars where the second bar can be rotated and is not restricted in its axial direction

Slim design maintains concrete cover

Installs quickly and easily

Multiple coatings available

技术参数

完成标准:	ASTM® A767 I 类
完成:	热浸镀锌
耦合器保护器:	标准
材料:	钢

Table 1/2

物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	六角宽度 (W)	直径 (Ø)	长度 (L)
-----	----------	----------	-----------	----------	--------	--------

EL12A2NGV	12 mm	#4	10M	17 mm		42mm
EL16A2NGV	16 mm	#5	15M	22 mm		56mm
EL20A2NGV	20 mm	#6	20M	27 mm		72mm
EL22A2NGV	22 mm	#7			32 mm	81mm
EL25A2NGV	25 mm	#8	25M		36 mm	86mm
EL28A2NGV	28 mm	#9	30M		40 mm	92mm
EL32A2NGV	32 mm	#10			45 mm	97mm
EL36A2NGV	36 mm	#11	35M		50 mm	102mm
EL40A2NGV	40 mm				55 mm	127mm
EL43TA2NGV	43 mm	#14	45M		60 mm	137mm
EL57TA2NGV	57 mm	#18	55M		80 mm	168mm
EL50TA2NGV	50 mm				70 mm	167mm


Table 2/2			
物料号	杆深 (BD)	杆间隙 (BG)	单位重量
EL12A2NGV	15mm	12mm	0.06 kg
EL16A2NGV	22mm	12mm	0.12 kg
EL20A2NGV	28mm	16mm	0.24 kg
EL22A2NGV	32mm	17mm	0.35 kg

物料号	杆深 (BD)	杆间隙 (BG)	单位重量
EL25A2NGV	34mm	18mm	0.45 kg
EL28A2NGV	38mm	16mm	0.58 kg
EL32A2NGV	40mm	17mm	0.76 kg
EL36A2NGV	43mm	16mm	0.99 kg
EL40A2NGV	55mm	17mm	1.38 kg
EL43TA2NGV	56mm	25mm	1.92 kg
EL57TA2NGV	71mm	26mm	4.14 kg
EL50TA2NGV	71mm	25mm	3 kg

其他产品详情

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE