

BEP Bar End Protector



Bar end protectors are placed onto the ends of threaded reinforcing steel bars. These protective caps help prevent damage to the nVent LENTON threads and help keep dirt and water out of the threads during storage, transportation and installation.

功能

Easy to install and remove

Color coded for the appropriate reinforcing bar size

技术参数

Table 1/1

物料号	订货号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	颜色
EL10BTP	370000	10 mm	#3		黄色
EL12BTP	370010	12 mm	#4	10M	红色
EL14BTP	370020	14 mm			绿色
EL16BTP	370060	16 mm	#5	15M	黑色
EL18BTP	370130	18 mm			白色
EL20BTP	370070	20 mm	#6	20M	黄色
EL22BTP	370140	22 mm	#7		蓝色

物料号	订货号	钢筋尺寸，公制	钢筋尺寸，美国	钢筋尺寸，加拿大	颜色
EL25BTP	370080	25 mm	#8	25M	红色
EL28BTP	370090	28 mm	#9	30M	黑色
EL30BTP	370100	30 mm			白色
EL32BTP	370150	32 mm	#10		黄色
EL34BTP	370160	34 mm			红色
EL36BTP	370110	36 mm	#11	35M	蓝色
EL38BTP	370170	38 mm	#12		白色
EL40BTP	370120	40 mm			绿色
EL43TBTP	370180	43 mm	#14	45M	红色
EL50TBTP	370190	50 mm			黑色
EL57TBTP	370200	57 mm	#18	55M	蓝色

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE