

ELFM Female-to-Male Extension



nVent LENTON ELFM Female-to-Male Extensions are a unique problem solver for the nVent LENTON taper-threaded splicing system. The extensions are ordered to customer specified lengths and are machined to have a female nVent LENTON taper thread on one end and a male nVent LENTON taper thread on the other. These extensions can be used in conjunction with the entire nVent LENTON taper threaded coupler product line to increase the length of either the reinforcing steel or nVent LENTON couplers.

功能

Small diameter reduces concrete cover and eliminates reinforcing steel bar (rebar) congestion

Tapered thread helps prevent cross-threading and provides a positive locking, no-slip connection

Installs quickly, taking approximately four and one-half turns to engage

No special tools or skills required

Available in customer specified lengths

技术参数

完成: 普通

材料: 钢

Table 1/2


物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	直径 (Ø)	长度 (L)	杆深 (BD)
EL25F25M125N	25 mm	#8	25M	35 mm	125mm	40mm
EL28F28M130N	28 mm	#9	30M	40 mm	130mm	42mm
EL32F32M138N	32 mm	#10		45 mm	138mm	45mm

Table 2/2	
物料号	单位重量
EL25F25M125N	0.6 kg
EL28F28M130N	0.8 kg
EL32F32M138N	1 kg

其他产品详情

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE