

T-Series Horizontal Low Slip Sleeve, Top Fill



The top fill, low slip horizontal T-Series sleeve length is increased to reduce slip (for extreme code requirements) and when the rib pattern or spacing does not meet the minimum product specifications.

Vent holes are added to horizontal sleeves to reduce air entrapment and help ensure proper filling of the sleeve.

功能

Designed to connect horizontal reinforcing bars and angular reinforcing bars up to 45 degrees

Used to splice the same diameter bars

Additional length improves performance

Works with saw cut, flame cut and sheared bars

Can be visually inspected after installation

技术参数

完成: 普通

材料: 钢

100% 美国国内内容: 是

Table 1/2

物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	直径 1 (Ø1)	直径 2 (Ø2)	长度 1 (L1)
RBW6555HA	16 mm	#5	15M	35 mm	22 mm	152 mm
RBW6556HA	20 mm	#6	20M	38 mm	25 mm	178 mm
RBW6557HA	22 mm	#7		41 mm	29 mm	178 mm

物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	直径 1 (Ø1)	直径 2 (Ø2)	长度 1 (L1)
RBW6558HA	25 mm	#8	25M	48 mm	32 mm	178 mm
RBW6559HA	28 mm	#9	30M	54 mm	38 mm	178 mm
RBW65510HA	32 mm	#10		57 mm	41 mm	191 mm
RBW65511HA	36 mm	#11	35M	64 mm	44 mm	203 mm
RBW65514HA	43 mm	#14	45M	76 mm	54 mm	229 mm
RBW65518HA	57 mm	#18	55M	95 mm	67 mm	279 mm


Table 2/2			
物料号	长度 2 (L2)	长度 3 (L3)	单位重量
RBW6555HA	76 mm	20mm	0.68 kg
RBW6556HA	89 mm	20mm	0.86 kg
RBW6557HA	89 mm	20mm	0.95 kg
RBW6558HA	89 mm	20mm	1.36 kg
RBW6559HA	89 mm	20mm	1.6 kg
RBW65510HA	95 mm	26mm	1.81 kg
RBW65511HA	102 mm	26mm	2.54 kg
RBW65514HA	114 mm	26mm	4.04 kg
RBW65518HA	140 mm	26mm	7.94 kg

其他产品详情

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE