

19" Pusher Fan, 2 U, Axial

Power Utilities

Fan tray with integrated pusher fan.



认证



功能

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

技术参数

Table 1/1

物料号	交流输入电压	直流输入电压
10713-534	230 V min	

物料号	交流输入电压	直流输入电压
10713-518	230 V min	
10713-526	230 V min	
10713-536	115 V min	
10713-520	115 V min	
10713-537		24 V min
10713-529		24 V min
19713-540		

其他产品详情

Please order mains cable separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE