

CPI 接地与连接不锈钢编织带，适用于大螺栓

电力公用事业



高质量 CPIW

不锈钢接地和连接编织带可安装于高腐蚀环境，如近海或沿海应用。整个系列的 CPIW

编织带尤其适用于使用不锈钢管道或不锈钢箱的应用，例如食品和饮料业、建筑业、交通、石油和化工业。

nVent ERIFLEX 提供的 316L

不锈钢编织带是市场上耐受性最高的不锈钢产品之一。我们专有的生产工艺已经过优化，可实现出众的编制、焊接和接片。

认证



功能

CPIW 具有出色耐磨损性、防腐性、耐化学性和抗紫外线性能，适用于户外应用

Covering from M20 (3/4"-10) up to M42 (1 1/2"-6) bolt fixation point

灵活和耐用的解决方案，适用于需要承受连续运动的伸缩接头

开箱即用，无需切割、剥离、卷边和冲孔

快速简易安装

耐振动、耐疲劳，减少维护

不会锈蚀或变色，因此外观永不褪色或改变

良好的电接触

不需要额外的接线片或端子

非磁性材料


EMC/EMI 指令推荐

Performs to the class C5 (very high) category as per ISO® 12944-2

符合 EAC 标准

符合《电气、电子设备中限制使用某些有害物质指令》(RoHS) 标准

图表



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.