

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

物料号

34566-284



Combinations of horizontal rails and side panels

$\text{+} = \text{can be combined}$
 $\text{+} = \text{combination not recommended}$

	Support 1	Support 2	Support 3	Support 4
Support 1		-	network 10 double network 10	network 10 support
Support 2		+	network 10 double network 10	+
Support 3		network 10 double	network 10 double	-
Horizontal rail				
Side panel	Support 1	Support 2	Support 3	Support 4

Support 1: 
 Support 2: 
 Support 3: 
 Horizontal rail: 
 Side panel: 

The rugged horizontal rail type can handle shock and vibration up to 25 g.

认证



功能

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

产品属性

产品类型: 水平横梁

产品系列: EuropacPRO

类型: 加固型, KD

机架宽度: 84 HP

长度: 431.8 mm

包装数量: 1

其他产品详情

Without M4 thread to front, without printing and without notch for 19" bracket.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE