

# RackPower 3x Temperature and 1x Humidity Sensor

## 电力公用事业

### 物料号

**EA9105**



适用于 nVent SCHROFF RackPower PDU 的 3x 温度和 1x 湿度探头传感器。

### 功能

3x Temperature and 1x Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

适用于 RackPower RP1xxx、RP2xxx、RP6xxx 系列 PDU

可热插拔，便于集成

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +/- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +/- 5 %

Second and Third Temperature Sensor with 950 mm cable

### 产品属性

产品类别：传感器

类型：温度和湿度

搭配：RackPower

## 警告

---

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**