


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

电力公用事业

用于安装背板的 EMC 屏蔽型插箱，重型版本带有 tox 焊接侧板。



认证



功能

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

提供改制，如开孔、各种表面或尺寸

扁平包装，节省空间

铝结构

“重”型水平横梁

用于安装背板的后水平横梁，带绝缘条

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

内部和外部尺寸符合：IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

技术参数

Table 1/3

物料号	机架高度	深度	包装数量	用于安装	板深度	EMC 垫片类型
24563-172	3 U	235 mm	1	背板	160 mm, 220 mm	泡棉
24563-173	3 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-174	3 U	355 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-472	6 U	235 mm	1	背板	160 mm, 220 mm	泡棉
24563-473	6 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-474	6 U	355 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉

Table 2/3

物料号	耐冲击和振动性	包含把手	安装	符合	EMC 屏蔽	产品类型
24563-172	5 g (force)	否	机架	IEC 60297-3-103	是	插箱/机箱
24563-173	5 g (force)	否	机架	IEC 60297-3-103	是	插箱/机箱
24563-174	5 g (force)	否	机架	IEC 60297-3-103	是	插箱/机箱
24563-472	5 g (force)	否	机架	IEC 60297-3-103	是	插箱/机箱
24563-473	5 g (force)	否	机架	IEC 60297-3-103	是	插箱/机箱
24563-474	5 g (force)	否	机架	IEC 60297-3-103	是	插箱/机箱

Table 3/3

物料号	机架宽度	静态负载
-----	------	------

24563-172	84 HP	15 kgf
24563-173	84 HP	15 kgf
24563-174	84 HP	15 kgf
24563-472	84 HP	15 kgf
24563-473	84 HP	15 kgf
24563-474	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

单个配置：支持大范围高度、宽度和深度；根据不同应用可选多种规格导轨；内部选项；附件和安装材料。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE